2171250

DATA SHEET

Valid from: 16.10.2019

IE-PNC-5-M12D-S-(L*)-P-2-22-FD-M12DF-S



Description

• Industrial Ethernet patchcord Cat.5, shielded

 Straight M12-jack, D-coded and straight M12-plug, D-coded

Based on ETHERLINE® Cat. 5 (2170894)



General characteristics

Connection method, connector M12-jack, D-coded

M12-plug, D-coded

Number of pins

Ambient temperature -30°C to +90°C (-22°F to +194°F)

Degree of protection IP 67, IP 69 (M12, plugged and locked)

Shielding Shielded
Conformity RoHS conform
REACH conform

LABS free

Variation

Data sheet also valid for variant lengths. Other lengths on request.

Article	Description	Length (L*) [m]
2171250	IE-PNC-5-M12D-S-0,5-P-2-22-FD-M12DF-S	0.5
2171251	IE-PNC-5-M12D-S-1-P-2-22-FD-M12DF-S	1
2171252	IE-PNC-5-M12D-S-2-P-2-22-FD-M12DF-S	2
2171253	IE-PNC-5-M12D-S-3-P-2-22-FD-M12DF-S	3
2171254	IE-PNC-5-M12D-S-5-P-2-22-FD-M12DF-S	5
2171255	IE-PNC-5-M12D-S-10-P-2-22-FD-M12DF-S	10
2171256	IE-PNC-5-M12D-S-20-P-2-22-FD-M12DF-S	20

Electrical properties

Rated voltage 50 V (max.) Rated current at 40 $^{\circ}$ C 1 A (max.)

Pollution degree 3 (M12, plugged and locked) 1 (RJ45, plugged and locked)

Transmission characteristics

Category (acc. product standard) 5

Creator: FELI1/PDP	Document: DB2171250EN	Page 1 of 4
Released: IVSE1/PDP	Version: 00	

2171250


DATA SHEET


Valid from: 16.10.2019


IE-PNC-5-M12D-S-(L*)-P-2-22-FD-M12DF-S



Connector pin assignment







Mechanical properties

M12-plug & -jack

Contact, material CuZn, gold plated
Nut, material CuZn, nickel plated
Handle, material TPU

Cable (Lapp article number: 2170894)



Design

Certification c(UL)us, type CMX acc. to UL 444 and VW-1 acc. to UL 1581 Conductor tinned copper, fine-wire stranded 7 x ca. 0,25 mm \emptyset (7/30 AWG),

ca. 0.75 mm conductor Ø (22 AWG)

Insulation PE, ca. 1.5 mm outer \emptyset

Core identification code acc. to IEC 60708-1; white, yellow, blue, orange

Stranding star quad, plastic tape

Inner sheath halogen free compound FRNC, ca. Ø 3,9 mm

Screen plastic laminated aluminum foil

on top:

braid of copper wire, tinned wire 0,10 mm - 0,15 mm, coverage

85 % ±5 %

Outer sheath PUR halogen free and flame retardant compound, green RAL 6018,

sheath-thickness ca. 0.9 mm, outer Ø: ca. 6.5 mm

Electrical properties at 20°C

Loop resistance max. 120 Ω /km, acc. to VDE 0812

Insulation resistance min. 0,5 $G\Omega$ xkm

Mutual capacitance nom. 52 nF/km (at 800 Hz

Characteristic impedance 100 Ω ±15 Ω (1MHz up to 100 MHz)

Velocity of propagation ca. 0,67 c

Creator: FELI1/PDP	Document: DB2171250EN	Dage 2 of 4
Released: IVSE1/PDP	Version: 00	Page 2 of 4

DATA SHEET

Valid from: 16.10.2019

2171250

IE-PNC-5-M12D-S-(L*)-P-2-22-FD-M12DF-S



Signal transit time <534 ns/100 m

Peak operating voltage 100 V (not for power purposes)

Test voltage core/core: 700 V

core/screening: 700 V

Mechanical and thermal properties

Minimum bending radius 8 x cable \emptyset

Temperature range moved: -20° C up to +60° C (-4°F to +140°F)

fixed installation: -30° C up to +70° C (-22°F to +158°F)

Flammability flame retardant acc. UL 1581 (VW-1)
Halogen free halogen free acc. to VDE 0472-815

General requirements

This cable is conform to the EU-Directive 2011/65/EU

(RoHS, Restriction of the use of certain hazardous substances).

Standards / Approvals

Product standard, M12-connector IEC 61076-2-101

2171250


DATA SHEET

Valid from: 16.10.2019


IE-PNC-5-M12D-S-(L*)-P-2-22-FD-M12DF-S




Technical drawing




Jack M12x1



Dimensional drawing



Complete Patchcord



Tin cut-out for torsional protection

Application range

Automation, industrial machinery and plant engineering

Note

Photographs are not true to scale and do not represent detailed images of the respective products.

Creator: FELI1/PDP	Document: DB2171250EN	Dogo 4 of 4
Released: IVSE1/PDP	Version: 00	Page 4 of 4