## **DATA SHEET**



### HITRONIC® PCF DUPLEX FD PNC PVC-PUR

DB28351702EN valid from: 01.11.2014

### 1. **Product Description**

Cable designation: AT-V(ZN)Y(ZN)11Y 2K200/230 flex J-V(ZN)Y(ZN)11Y 2K200/230 flex

Splittable duplex polymer cladded glass optical fibre (PCF) indoor cable with non-metallic strain relief, PVC inner and PUR outer sheath, for applications in industrial environments with high mechanical stress, suitable for drag chains

### 2. **Application**

PCF bus cable for PROFINET applications; Type C special applications (highly flexible, permanent movement) Applications with cable lengths up to 100m at 100Mbit/s data rate For direct connector assembly (single cable diameter 2.2 mm)

### 3. Cable Design



Cable construction	2x PCF fibre (polymer cladded fibre with ETFE buffer), non-metallic strain relief elements, PVC single cable sheath, stranded with two filler elements and central element, plastic fleece as wrapping, strain relief elements, PUR outer sheath	
Cable inner sheath	PVC (special PVC-based compound)	
Cable outer sheath	PUR ( Polyurethane ) mat, halogen-free	
Colour of inner sheath	See colour coding	
Colour of outer sheath	Green (similar to RAL 6018)	
Colour coding	Black, orange (with arrow printing)	
Strain relief	Aramid yarns (in single and total cable construction)	
Type of armouring	-	

### 4. **Optical and Physical Properties of Fibre**

Attenuation	@ 650 nm	dB/km	≤ 10
	@ 850 nm	dB/km	≤ 8
Bandwidth	@ 650 nm	MHz x km	≥ 17
	@850 nm	MHz x km	≥ 20
Numerical Aperture			0.37
Core diameter		μm	200
Cladding diameter		μm	230

### 5. **Thermal Properties**

Operating temperature	-20°C up to +70°C
Installation temperature	-10°C up to +50°C
Storage temperature	-30°C up to +70°C

Originator: JUBE / PNM	Dogument	DB28351702EN	nogo 1 of 2
approved: HAPF / PDC	Document:	DB26331702EN	page 1 of 2

# **DATA SHEET**



## HITRONIC® PCF DUPLEX FD PNC PVC-PUR

DB28351702EN valid from: 01.11.2014

#### 6. **Mechanical Properties**

Max. number of fibres			2	
Fibre outer diameter (with buffer)			500 μm	
Sub cable outer diameter			2.2 mm	
Cable outer diameter			8.8 ± 0.3 mm	
Cable weight			71 kg/km	
Min. bending radius		once several times	130 mm 175 mm	
Max. tensile strength	fixed installation short term		800 N 1.000 N	
Max. lateral pressure	fixed installation short term		3.000 N/10 cm 5.000 N/ 10 cm	
For use in drag chains*		bending cycles chains length speed acceleration	> 5.00.000 4.5 m 3 m/s 3 m/s <sup>2</sup>	
* Please note assembly guidelines T3 (LAPP main catalogue)				

### 7. **Chemical Properties**

PVC sub unit sheath	Non-aging, flame retardant, abrasion resistant
PUR outer sheath	Flame-retardant, halogen-free, oil resistant, low adhesion

#### 8. **Features**

- RoHS compliant
- Oil resistant according to IEC 60811-2-1 and DIN EN 50363-10-2 (100°C, 168h)
- PROFINET Optical Fibre Cable Type C according to guideline "PROFINET Cabling and Interconnection Technology" Version 3.1 March 2014
- EC-Directive: This cable is conform to the 2011/65/EU (RoHS, Restriction of the use of hazardous substances)

### 9. **Product Range Overview**

Part number	Article designation	No. Of Fibres	Outer ∅ (mm)
28351702	HITRONIC® PCF DUPLEX FD PNC PVC-PUR	2	8.8

Originator: JUBE / PNM	Document:	DB28351702EN	naga 2 of 2
approved: HAPF / PDC	Document.	DB20331702EN	page 2 of 2