DATA SHEET

AB-C4-M12MS-M16-0,5



Description

Valid from:

17.09.2018

 Sensor/Actuator flush-type plug, 4-pos., A-coded, M12 quick locking

 Front/screw mounting with M16 thread, with 0.5 m TPE litz wire, 4 x 0.34 mm²



General characteristics

Number of poles 4

Connection type Fixed connection

Status indicator No

Coding A-standard
Degree of protection IP 67
Inflammability class acc. to UL 94 V0

Ambient temperature (operation) -25 to +90 °C (-13 to 194 °F) (connector)

-25 to +85 °C (-13 to 185 °F) (cable fixed installation)

Electrical properties

 $\begin{array}{ll} \mbox{Insulation resistance} & \mbox{20 m} \Omega^* km \\ \mbox{Contact resistance} & \mbox{3 m} \Omega \end{array}$

Mechanical properties

Connector

Contact, material CuZn
Contact surface, material Au
Contact carrier, material PA66 GF

Knurl, material Zinc die-cast (nickel-plated)

Sealing, material NBR

Line

Cable type TPE litz wire

Conductor, material Tin plated copper litz wires

Core insulation, material PE
Conductor diameter including insulation 1.2 mm
Conductor cross section 0.34 mm²
AWG signal line 22

| Creator: MOKO2/PDP | Document: DB22260108EN | Page 1 of 2 |
|---------------------|------------------------|-------------|
| Released: IVSE1/PDP | Version: 03 | |


| 22260108 | DATA SHEET |
|-------------|-------------------|
| Valid from: | AD C4 M12M6 M14 O |


AB-C4-M12MS-M16-0,5





Technical drawing

17.09.2018









Application range

Connection of enclosures and cabinets

Note

Photographs are not true to scale and do not represent detailed images of the respective products.

| Creator: MOKO2/PDP | Document: DB22260108EN | Page 2 of 2 |
|---------------------|------------------------|-------------|
| Released: IVSE1/PDP | Version: 03 | |