

52104980	<b>DATA SHEET</b>	
Valid from: 06.06.2023	<b>SKINDICHT® SVRE-M</b>	

The SKINDICHT® SVRE-M brass cable gland is a cable entry for the universal use. The gland with hexagonal fitting and variable incised sealing ring offers a fast assembly with a flat spanner.



### Components:

Gland body	Brass, nickel plated
Pressure screw	Brass, nickel plated
Pressure washer	Steel, zinc-plated
Incised sealing ring	CR

### Technical features:

Connecting thread	M16x1,5 up to M63x1,5 acc. to EN 60423 <i>On request: Cable gland is also available with long connecting thread – SKINTOP® SVRE-M XL</i>
Functional thread	PG-thread acc. to DIN 40430
Protection class	IP54 acc. to EN 60529
Temperature range	-20 °C to +80 °C

### Norm references:




For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Creator: FICE1 /PDP Released: VACH1/PDP	Document: DB52104980EN Version: 04	Page 1 of 2
--	---------------------------------------	-------------

52104980	<b>DATA SHEET</b>	
Valid from: 06.06.2023	<b>SKINDICHT® SVRE-M</b>	

**Product drawing:**



**Dimension table:**

M Connecting thread	PG Function thread	SW1 [mm]	SW2 [mm]	Ø E [mm]	D [mm]	C [mm]	Ø F [mm] Incised sealing ring	Ø B [mm]	Article No.
M16x1,5	PG9	18	15	20	5	21,6	5 / 8	10	52104980
M20x1,5	PG11	22	18	24	6	23,6	7 / 10 / 12,5	12	52104990
M20x1,5	PG13,5	22	20	24	6	25,6	7 / 10,5 / 13 / 16	14	52105000
M20x1,5	PG16	24	22	26,2	6	26,6	8 / 10,5 / 13,5 / 16	15	52105010
M25x1,5	PG21	30	28	33	7	29,6	11 / 15 / 18 / 20	20	52105002
M32x1,5	PG29	40	37	42,5	8	32,6	18 / 23 / 27 / 31	27	52105003
M40x1,5	PG36	50	47	54	8	37,6	24 / 28 / 31 / 35	34	52105004
M50x1,5	PG42	57	54	60	9	42,6	30 / 35,5 / 39 / 42,5 / 46	43	52105005
M63x1,5	PG48	66	60	70	10	45,1	36 / 40 / 44 / 47 / 50,5	48	52105006

Creator: FICE1 /PDP Released: VACH1/PDP	Document: DB52104980EN Version: 04	Page 2 of 2
--	---------------------------------------	-------------