DATA SHEET



ETHERLINE® TRAY CAT. 7

UDB2170472EN

Date: January 1, 2020

1. APPLICATION

ETHERLINE® TRAY CAT.7 (bandwidth up to 600 MHz) is designed for stationary applications with class "F" performance and maximum transfer rate (IEEE 802.3) of 10 GBit/s up to 328 feet. Pairs are individually foil shielded with and overall braid shield; offering excellent shielding properties based on IEC 61156-5 and can be used in areas where reliable transmission is key including EtherNet/IP, Profinet with 4 pairs, EtherCAT, Power over Ethernet (IEEE 802.3af) and Power over Ethernet Plus (802.3at). Meets or exceeds the requirements for Cat. 6A per ANSI/TIA 568.2-D.

Applications:

Flexible applications, cable trays, industrial machinery, commercial and plant infrastructure

Underwriters Laboratories

For Tray use in power limited applications and internal or external wiring of electrical and electronic equipment.

Canadian Standards

For use as communications control, Appliance Wiring Material and internal or external wiring of electrical and electronic equipment applications.

2. CABLE DESCRIPTION

- Bare copper Solid strand
- Foam PE insulation
- 4 individually shielded twisted pairs
- Color coded conductors
- Overall TC Braid Shield
- Green (RAL 6018) UV and flame resistant specially formulated PVC jacket

3. TECHNICAL DATA

Conductor Stranding 22 AWG (0,34 mm²): Solid Strand

Design / Make-up Cable is designed in accordance with the requirements of UL Standards

13 and 444; and with CSA standard C22.2 No. 214

Insulation Foam Polyethylene insulation

Nominal Insulated Conductor OD: .061"

Shielded twisted Pairs 2 conductors cabled together with foil shield

Color Code Pair 1: White/Blue & Blue

Pair 2: White/Orange & Orange Pair 3: White/Green & Green Pair 4: White/Brown & Brown

Shield Tinned Copper Braid Shield (85% coverage)

Outer Sheath Specially formulated PVC jacket

Nominal Jacket Wall Thickness: .032" Nominal Overall Cable OD: .350"

Nominal Voltage UL/CSA: 300V

UL/CSA AWM: 600V

IEC: Not for power applications

Engineer: D. Kocheta
Approval: J. Gavilanes

Document: UDB2170472EN

Page 1 of 2

Lapp USA

DATA SHEET



ETHERLINE® TRAY CAT. 7

UDB2170472EN Date: January 1, 2020

Test Voltage 1500V

Min Bend radius For stationary use: 10 x Cable OD

For flexible use: 15 x Cable OD

Temperature Range For stationary use: -40°C to +80°C

For flexible use: -20°C to +80°C

Cable Attributes OR-03, FR-03, FL-01, MP-02

Sunlight resistant

Approvals UL AWM 21695 (Appliance Wiring Material) per UL 758

UL PLTC (Power Limited Tray Cable) per UL 13 UL CMG (Communications Cables) per UL 444

c(UL) CMG per CSA C22.2 No. 214

cRU AWM II A/B FT4 per CSA C22.2 No. 210

Additional RoHS directive